

The Birchwood Advantage

Award-Winning Lighting Solutions Backed By World Class Service & Support





The Birchwood Advantage

- 5 10-Day Shipping
- 6 Product Comparison Overview

Products

- 8 BW165
- 10 Collin
- 14 Nolan
- 18 Jake
- 20 Nathan
- 22 Vanessa
- 24 Michelle
- 26 Madeline

Welcome to Birchwood Lighting Anaheim, California

Since 1993, Birchwood Lighting has designed and manufactured quality specification-grade light fixtures tailored to meet the demands of the architectural, commercial, retail and interior lighting design communities. During these years we have remained steadfast in our commitment to developing and maintaining strong relationships with our customers and to providing the lighting marketplace with the best products available.







Prompt In-House Customer Service





STANDARD PRODUCT

10-DAY SHIPPING

Direct, Direct/Indirect and Recessed Linear

Program Details

Birchwood Lighting's 10-Day Shipping Program consists of some of our most popular architectural luminaires in varies sizes and options. By utilizing our new state-of-the-art manufacturing facility and expanded company resources, we are able to provide an impressive array of products capable of shipping in 10 days. Our dedicated and experienced inside team offers complete specifications that include drawings as well as photometric files, giving you the ability to satisfy tight project schedules.

Product Comparison Overview

11000	Profile (inches)	Profile Shape	Output	Output Type	Optics	Lens Type	Trim Type	Mounting	Light Source Feature
SUSPENDED/SU	JRFACE LINE	EAR							
BW165	1.65	Rectangle	500-1000 lm/ft	Direct/ Indirect	High Efficiency, Batwing 115°, Asymmetric 15°, 70° Elliptical	High Efficiency, Batwing 115°, Asymmetric 15°, Elliptical 70°	-	Cable Suspended, Wall Mount	Tunable White
Collin	1.25 2.25 3.25	Rectangle	481-987 lm/ft	Direct/ Indirect	High Efficency, Batwing, Asymmetric 15°, 70° Elliptical	Frosted White, High Efficiency, Reveal Frosted White 3/8" Extended, Batwing 115°,	-	Cable Suspended, Surface Mount	-
Kelsey	1.25 2.25 3.25	Square	481-987 lm/ft	Direct	High Efficiency, Batwing, Asymmetric or 70 Elliptical	Regressed, Frosted White or Flat Blade Louver	-	Cable Suspended, Surface Mount, Rotational Arm Mount	RGBW
Nolan	1.25 2.25 3.25	Square	314 -955 lm/ft	Direct	High Efficiency	Frosted White Tri-Sided	-	Cable Suspended, Surface Mount	
Charlotte	3.25	Rectangle, Square	400-1512 lm/ft	Direct/ Indirect	-	Frosted White	-	Cable Suspended, Surface Mount (Direct)	-
Hailey	1.25 2.25 3.25	Circlular	283-565 lm/ft	Direct	-	Frosted White, High Efficiency, Reveal Frosted White 3/8" Extended, Batwing 115°,	-	Cable Suspended, Rotational Arm Mount	-
Chloe	2.25 4.75	Circlular	103-1860 lm/ft	Direct/ Indirect	High Efficiency	Frosted White	-	Cable Suspended, Rotational Arm Mount	-

	Profile (inches)	Profile Shape	Output	Output Type	Optics	Lens Type	Trim Type	Mounting	Light Source Feature
RECESSED LII	NEAR								
Jake	1.65 2.25 3.25 5.00	Square/ Rectangle	250-1000 lm/ft	Direct, Wall Wash, Wall Graze	High Efficiency, Batwing, Asymmetric or 70° Elliptical	Regressed, Frosted White or Flat Blade Louver	Trim or Trimless	Recessed, T-Grid or Perimeter	RGBW
Jill	1.65 2.25 3.25 5.00	Square or Teardrop	250-1000 lm/ft	Direct, Wall Wash, Wall Graze	-	Frosted White, Tear Drop Frosted White, Reveal Frosted White 3/8 Extended or Drop Lens Asymmetrical	Trim or Trimless	Recessed, T-Grid or Perimeter	-
LEDGE / COV	Ξ								
Nathan	5.25	Rectangle	464-893 lm/ft	Narrow Distribution, Wide Distribution	Standard	Diffuser, Refractor	-	Surface Mount	-
Ashley	7.00	Rectangle	510-980 lm/ft	Narrow Distribution, Wide Distribution	Standard	Diffuser/Refactor	-	Surface Mount	-
LINEAR WET	LOCATION								
Vanessa	4.00	Square	393-756 lm/ft	Direct	High Efficiency	Frosted White	-	Cable Suspended, Surface Mount, Mullion Mount	
Brandi	2.75	Rectangle, Teardrop	489-937 lm/ft	Direct	High Efficiency	Frosted White	-	Surface Mount	-
ARCHITECTU	RAL PEND	ANTS							
Michelle	4.00	Disk	-	Direct/ Indirect	Standard	-	-	Cable Suspended, Surface Mount	RGB (Uplight Only)
Katrina	4-3/16 6.00	Square, Rectangle	-	Direct/ Indirect	High Efficiency	-	-	Cable Suspended, Surface Mount (Direct)	-
Madeline	1.625	-	491-1080 lm/ft	Direct/ Indirect	Standard	-	-	Cable Suspended, Surface Mount	-
Erika	1.25 2.25 3.25	Square, Rectangle, Round	283-942 lm/ft	Direct/ Indirect	High Efficiency	Frosted white, Flush Lens, Reveal, Tri-Sided	-	Cable Susptended, Surface Mount	-



BW165 Small Profile Direct/Indirect

The highly configurable and easy to specify BW165 offers clean straight lines, mitered corners, an integral driver with deep dimming and 90CRI all standard. An innovative continuous run latching system combined with light leak baffles ensures uninterrupted straight lines in a system that is virtually effortless to install and maintain.

Mounting Options

- Cable Suspension
- ADA Compliant Wall Mount

Light Source Features

- 250 lm/ft or 1000 lm/ft with Custom Lumen Outputs Between 250 1000 lm/ft
- 82 CRI in 3000K, 3500K or 4000K
- 92 CRI in 2700K, 3000K, 3500K or 4000K
- Tunable White from 2700K 6500K

Profile Size End Cap Options



Performance Optics & Lens Options





Collin Direct/Indirect Linear

Collin is designed to deliver strong and even illumination while "disappearing" into any architectural interior surrounding. Concealed within COLLIN's modern profile is a true workhorse fixture that can deliver multiple direct or indirect lighting options, and is available in either 1.25", 2.25" or 3.25".

Mounting Options

- Cable Suspended
- Wall Mount



Profile Size



Performance Optics & Lens Options



Flat Blade Louver Direct Only









Kelsey Square Architectural

Incredibly versatile and efficient with numerous options and variations, Kelsey linear luminaires deliver timeless design and modern efficiency from within a smooth and elegant square profile. Choose from 1.25", 2.25" or 3.25" squared smooth extruded aluminum profiles with a choice of frosted extruded acrylic lenses or semi-specular flat blade louver.

Mounting Options

- Cable Suspended
- Powered Cable Suspension
- Surface Mount
- Wall Mount
- Cable Suspended Rotational
- Surface Mount Rotational

Light Source Feature

RGBW Capable (4000K White at 90 CRI)

Profile Size



Performance Optics & Lens Options





Nolan Linear Wrap Lens

NOLAN provides specification grade design and luminance to the refined architectural market. The precision-edged extruded acrylic lens satisfies the sharp sophisticated design aesthetic required by lighting specifiers, yet also provides effortless removal and exact snap-in lens replacement every time.

Mounting Options

- Cable Suspended
- Surface Mount
- Powered Cable Suspension







Charlotte Direct/Indirect Curves



Charlotte's sweeping curved profile features multiple distribution and LED options within a 3.25" extruded aluminum housing. Unleash your creativity using broad curves and shapes with the continuous run option or as a stand alone luminaire add visual interest to your space by creating dramatic architectural patterns. Charlotte offers smooth direct or direct/indirect illumination within its curved, streamlined architectural profile.

Mounting Options

- Cable Suspended
- Surface Mount





Hailey Round Linear

Hailey's elegant round linear profile offers a large variety of mounting and lens options. Rotational function combined with arm (RAS), cable (CSS-R) or stack light (STK-RAS) mounting can allow up to 361° lockable aiming for precise light distribution on the vertical, horizontal or ceiling plane. Continuous run installations provide endlessly straight runs while delivering efficient illumination.

Mounting Options

- Cable Suspended
- Powered Cable Suspension
- Rotational Arm Wall Mount





Chloe Direct/Indirect Round Linear



Chloe is designed to perfectly deliver direct and indirect light to the ceiling, wall or work plane. Chloe is comprised of heavy gauge extruded anodized aluminum, extruded acrylic lenses and 1/4" precision machined smooth aluminum end caps designed to conceal all hardware and fittings.

Mounting Options

- Cable Suspended
- Surface Mount



Jake **Recessed Linear Luminaire**

Jake is a recessed linear luminaire that seamlessly installs into drywall, hard ceiling and T-grid applications. Jakes is comprised of various apertures, mounting options and optics, and is also available in wall wash or wall glaze configurations.

Mounting Options

Recessed - Mud In, Trim, T-Grid

Light Source Feature

RGBW 4000K at 90 CRI

Profile Size



Wall Graze & Wall Wash Only

5.00"



High Efficiency

(HE)



Efficacy: Up to 115lm/W Beam:115°



Performance Optics & Lens Options



Efficacy: Up to 112lm/W Beam: 15°



Efficacy: Up to 109lm/W





Up to 105lm/W Beam: 70°

Frosted White



up to 95lm/W





Jill Drop-Lens Recessed Linear Luminaire



Elusive and revealing: Jill and Jill Asymmetric (ASYM) combine the best of both qualities within striking, slender apertures that almost dissolve into the ceiling, yet still unveil a subtle glow from their unique dropped-lens features.

Mounting Options

Recessed - Mud in, Trim, T-Grid





Nathan Indirect Ledge Linear

The strength of Nathan is the purposeful cove-lighting capability encased within a solid sleek modern shroud. Suitable for wall mounting in any interior application or use as a window trimming or illuminated ledge effect.

Mounting Options

Wall Mount

Profile Size

5.25"





Ashley Linear Cove Lighting



Ashley features tool-less adjustable aiming up to 15° in 5° increments with distribution available in wide or narrow optics for various cove lighting requirements. With efficient precise illumination capabilities, easy installation and a variety of housing profiles, Ashley makes it possible to realize excellent cove lighting.

Mounting Options

Surface Mount

Profile Size

7"



Vanessa Architectural Wet Location

A strong, elegant wet location luminaire designed to complement wet exterior or interior installations, Vanessa is IP65 rated and built to last. Weather-sealing prevents water and moisture from entering the lens, power entry points and endcaps. Vanessa is also available wall wash and wall graze configurations.

Mounting Options

- Cable Suspended
- Wall Mount
- Surface Mount
- Mullion Mount







Brandi Wrap Lens Wet Location



Compact yet thoroughly robust, Brandi is designed for architectural applications which demand a performance-driven IP65 rating. Various mounting orientations make installations in hard-to-reach areas less harrowing and allow for even illumination.

Mounting Options

• Surface Mount (Ceiling or Wall in Vertical or Horizontal Orientation)





Michelle Low Profile Disk



48"

Featuring fully programmable drivers, the 4' MICHELLE is capable of exceeding 40,000 lumens with dimming to 1%. On the indirect side, add an extra pop of color with optional RGB or get up to 5000 lumens in typical white CCT's. Engineered to reduce glare and eliminate pixilation, the vacuum formed single piece lens is field adjustable from flush to 5/8" drop.

Features

- Flush Lens, or 5/8" Field Adjustable Drop Lens
- Vacuum formed, Single Piece Acrylic Lens
- Spun Aluminum Driver Housing
- RGB Capable at 4000K-2700K (Uplight Only)

Mounting Options

- Cable Suspended
- Cable Suspended Mono Point
- Surface Mount



Mounting Options



Cable Suspended



Cable Suspended Mono Point



Surface Mount

Katrina Direct/Indirect



Comprised of a single piece acrylic lens, aluminum housing, integral driver, multiple color temperatures and custom lumen outputs, Katrina offers an elegant, architecturally pleasing design while delivering efficient and even light distribution. Suspended horizontally with aircraft-cable and offering optional direct and indirect switching capability, Katrina produces dual continuous rings of light from a 5/8" extended lens from a 6" tall housing.

Mounting Options

- Cable Suspended
- Cable Suspended Mono Point
- Surface Mount

Madeline Dynamic Freeform

A creative and versatile luminaire, Madeline is sleek and beautiful as a standalone fixture or let your imagination run free to design shapes, circles, and ovals able to fit any space. Using uniquely illuminated convex and concave radial sections, Madeline easily generates dynamic, flowing undulations. Constructed of heavy gauge extruded aluminum and featuring our highest quality precision machined aluminum end-caps.

Features

- High Efficiency Lens
- Batwing & Indirect Batwing
- Asymmetric 15 Degree
- Elliptical 70 Degree

Mounting Options

- Cable Suspended
- Surface Mount





Dynamic Form Variations



Concave



Convex





4' Diameter Ring

8' Diameter Ring



Erika Linear Shapes



Offering show-stopping elegance within a dynamic geometric shape and profile, Erika creates a sensational lasting impression in any interior application. Horizontally cablesuspended or surface mounted, Erika can be specified in either square or rectangular shapes constructed of 1.25", 2.25" or 3.25" mitered extruded aluminum.

Mounting Options

- Cable Suspended
- Surface Mount

Options

Custom Shape Capabilities

Profile Size



Lens Options







Direct Reveal Lens



Direct/Indirect Flush Lens



Direct/Indirect Reveal Lens



Tri-Sided Lens



Rounded Profile Lens













BirchwoodLighting 3340 E. La Palma Ave. Anaheim, CA 92806

tel 714 630-9877 **fax** 714 630-9883

info@birchwoodlighting.com www.birchwoodlighting.com

A Leviton Company www.leviton.com

Printed in the U.S.A Copyright © 2021. Intense Lighting, LLC. All Rights Reserved.

BW0621-ADV-1